# MONOLED-BT/ DUOLED-BT HIGHLIGHTS

Superb audio Bluetooth headset with USB-C standing dongle and busy light information.

Notes:

- It is required to install WIService (Collaboration -> Settings -> Extensions) to use MonoLED-BT/ DuoLED-BT.
- MonoLED-BT headset is available only as HWaaS.

### **FEATURES**

- Status LEDs: online, away, DND, on call, ringing, call hold, missed call
- Answer/ Hangup/ Mute/ Volume control buttons
- Bluetooth 4.2, advanced multipoint
- Wideband audio frequency

### • Ultra noise canceling mic

- Up to 30m wireless range
- Talking time up to 15 hours
- High-performance 6th generation CVC technology



## MONOLED-BT/ DUOLED-BT - TECH SPECIFICATIONS

#### CONNECTIVITY

Bluetooth 4.2 advanced multipoint Range: up 30 meters

Frequencies: 2.4 GHz-2.480 GHz

Profiles: HSP 1.2, HFP 1.6, A2DP

#### POWER and BATTERY

Talking time: up to 15 hours; Standby time: up to 20 hours; Charging time: approx. 3.5 hours

Type: Lithium-ion polymer

Capacity: 300 mA per hour standard

Charging method: USB Type-C (Type-A adapter included)

#### AUDIO

Wideband audio frequency

Noice cancelling mic

Advanced hearing protection with safetone™

Crystal clear sound and voice DSP

High-performance 6th generation CVC technology

Tone control

Frequency: 100-12KHz

Speaker Impedance: 32Ω

Speaker Sensitivity 1kHz: 96±3dB

Microphone Sensitivity 1kHz: -50±2dB

### ENVIRONMENTAL

Working: 0  $^{\circ}$  C to +40  $^{\circ}$  C; up to 95% relative humidity, non-condensing Battery operating: -20  $^{\circ}$  C to +60  $^{\circ}$  C

#### PHYSICAL

Weight: 286/ 307g (Headset and Base Station)

Size:

Headset:174\*143\*30mm

Base:121\*69\*195mm

Visual indicators: LED indicates call status, pairing status and others

Beep: indicate volume level, microphone mute, and others

#### COMPATIBILITY

WorkForce

WelcomeConsole

Vision, SuperVision \*

Apple Mac, Windows PC

Android, iOS apps (without support of LED user statutes)

W-AIR LifeSaver, W-AIR Med, W-AIR Office (without support of LED user statutes)

\*Current limitation: To change volume on MonoLED-BT/ DuoLED-BT, use volume buttons on Vision/ SuperVision

Phones Accessories datasheets:

